



Product Information

Pneumati-Sifter Centrifugal Separator

KASON CORPORATION
67-71 East Willow St.
Millburn, NJ 07041-1416
USA
Tel: 973-467-8140
Fax: 973-258-9533
E-mail: info@kason.com

**KASON CORPORATION,
EUROPE**
Block 4, Units 12 & 13
Park Hall Business Village
Park Hall Road
Longton, Stoke-on-Trent
Staffordshire, ST3 5XA
UNITED KINGDOM
Tel: 1782-597540
Fax: 1782-597549
E-mail:
sales@kasoneurope.co.uk

SEPARATOR ENGINEERING LTD.
6025 Boul Thimens
Saint Laurent
Quebec
CANADA
H4S 1V8
Toll Free (Canada only):
877-694-4441
Tel: 514-667-6777
Fax: 514-745-2074
E-mail:
info@separatorengineering.com



www.kason.com

Pneumati-Sifter Centrifugal Separator

Screens in-line with pneumatic conveying systems at high rates

The Pneumati-Sifter centrifugal separator de-agglomerates and screens materials in-line with dilute-phase pneumatic conveying systems, eliminating the need for cyclone separators and rotary air locks. It is rated for positive pressures to 14.9 psig (1 barg) or negative pressures to 14" (356mm) vacuum. Rotating helical paddles continuously propel material through apertures in a cylindrical screen. Oversize particles are ejected via a manual or automatic valve into a sealed, quick release receptacle.

Options:

- Anti-blinding devices
- Clean-in-place (CIP)
- Twin centrifugal configuration
- Design, construction and finish to FDA, 3-A, BISSC, EEC and other sanitary standards
- Belt drive and Direct drive configurations
- Design, construction and finish to pharmaceutical specifications

